



# Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Stainless Steel, 2.00-2.49"

By Bryant  
Catalog # [SHC200DES](#)

Wire and Cable Management, Support Grips, Heavy Duty,  
Double Eye, Stainless Steel, 2.00-2.49"



## Application

Double Eye

## General

Approx Breaking Strength	20,100 lbs
Construction	Woven
Material	Stainless Steel
Material - Mounting Hardware	Screw Hook or Beam Clamp
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Closed Mesh, Double Weave
Type	Double Eye
UPC	781786007000

## Conductor Related

Cable Diameter Range	2 in-2.49 in
Cable Size	2.00-2.49" (5.08-6.32)

## Logistics

Carton Quantity 5

## Product Assets

[Catalog Page - Bryant N-9 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

- [SHC300DES - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Stainless Steel, 3.00-3.49"](#)
- [SHC250DES - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Stainless Steel, 2.50-2.99"](#)
- [SHC250 - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, 2.50-2.99"](#)
- [SHC075 - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, 0.75-0.99"](#)
- [SHC450 - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, 4.50-5.00"](#)



A proud member of the Hubbell Family.