



Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, 4.00- 4.49"

By Bryant
Catalog # [SHC400](#)

Wire and Cable Management, Support Grips, Heavy Duty,
Double Eye, Tin-Coated Bronze, 4.00-4.49"



Application

Double Eye

General

Approx Breaking Strength	12,070 lbs
Construction	Woven
Material	Stainless Steel
Material - Mounting Hardware	Screw Hook or Beam Clamp
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Closed Mesh, Double Weave
Type	Double Eye
UPC	781786244085

Conductor Related

Cable Diameter Range	4 in-4.49 in
Cable Size	4.00-4.49" (10.16-11.40)

Product Assets

[Catalog Page - Bryant N-9 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

- [SHC125 - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, 1.25-1.49"](#)
- [SHC100 - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, 1.00-1.24"](#)
- [SHC200DES - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Stainless Steel, 2.00-2.49"](#)
- [SHC125U - Wire and Cable Management, Support Grips, Heavy Duty, Single Eye, Tin-Coated Bronze, 1.25-1.49"](#)
- [SHC450 - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, 4.50-5.00"](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-SHC400-SPEC-EN | REV 7/2023