



# Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, 4.50- 5.00"

By Bryant  
Catalog # [SHC450](#)

Wire and Cable Management, Support Grips, Heavy Duty,  
Double Eye, Tin-Coated Bronze, 4.50-5.00"



## Application

Double Eye

## General

Approx Breaking Strength	13,790 lbs
Construction	Woven
Material	Stainless Steel
Material - Mounting Hardware	Screw Hook or Beam Clamp
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Closed Mesh, Double Weave
Type	Double Eye
UPC	781786244207

## Conductor Related

Cable Diameter Range	4.5 in-5 in
Cable Size	4.50-5.00" (11.43-12.70)

## Product Assets

[Catalog Page - Bryant N-9 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

- [SHC400 - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, 4.00-4.49"](#)
- [SHC075U - Wire and Cable Management, Support Grips, Heavy Duty, Single Eye, Tin-Coated Bronze, 0.75-0.99"](#)
- [SHC300DES - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Stainless Steel, 3.00-3.49"](#)
- [SHC200DES - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Stainless Steel, 2.00-2.49"](#)
- [SHC125U - Wire and Cable Management, Support Grips, Heavy Duty, Single Eye, Tin-Coated Bronze, 1.25-1.49"](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-SHC450-SPEC-EN | REV 7/2023