



Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, Lace Closing, 1.25-1.49"

By Bryant
Catalog # SHS125

Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, Lace Closing, 1.25-1.49"



Application

Double Eye

General

Approx Breaking Strength	4,280 lbs
Construction	Woven
Material	Bronze, Tin Coated
Material - Mounting Hardware	Screw Hook or Beam Clamp
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Split Mesh, Lace Closing
Type	Double Eye
UPC	781786244542

Conductor Related

Cable Diameter Range	1.25 in-1.49 in
Cable Size	1.25-1.49" (3.17-.378)

Logistics

Carton Quantity 5

Product Assets

[Catalog Page - Bryant N-10 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

- [SHS300 - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, Lace Closing, 3.00-3.49"](#)
- [SHS150 - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, Lace Closing, 1.50-1.99"](#)
- [SHS075 - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, Lace Closing, 0.75-0.99"](#)
- [SHS400 - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, Lace Closing, 4.00-4.49"](#)
- [SHS150U - Wire and Cable Management, Support Grips, Heavy Duty, Single Eye, Tin-Coated Bronze, Lace Closing, 1.50-1.99"](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-SHS125-SPEC-EN | REV 7/2023