



Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, Lace Closing, 2.00-2.49"

By Bryant
Catalog # SHS200

Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, Lace Closing, 2.00-2.49"



Application

Double Eye

General

Approx Breaking Strength	8,050 lbs
Construction	Woven
Material	Bronze, Tin Coated
Material - Mounting Hardware	Screw Hook or Beam Clamp
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Split Mesh, Lace Closing
Type	Double Eye
UPC	781786244580

Conductor Related

Cable Diameter Range	2 in-2.49 in
Cable Size	2.00-2.49" (5.08-6.32)

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - Bryant N-10 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

- [SHS125U - Wire and Cable Management, Support Grips, Heavy Duty, Single Eye, Tin-Coated Bronze, Lace Closing, 1.25-1.49"](#)
- [SHS125 - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, Lace Closing, 1.25-1.49"](#)
- [SHS350 - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, Lace Closing, 3.50-3.99"](#)
- [SHS075 - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, Lace Closing, 0.75-0.99"](#)
- [SHS150 - Wire and Cable Management, Support Grips, Heavy Duty, Double Eye, Tin-Coated Bronze, Lace Closing, 1.50-1.99"](#)



A proud member of the Hubbell Family.