



Circuit Watch Surge Suppression Straight Blade Receptacle, Industrial/Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, Ivory

By Bryant
Catalog # [SP52IA](#)



Circuit Watch Surge Suppression Straight Blade Receptacle,
Industrial/Commercial Grade, 15A 125V, 2-Pole 3-Wire
Grounding, 5-15R, Ivory

Application

Duplex with Light and Alarm

General

Color	Ivory
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED and Audible Alarm
Item Type	Surge Protection Receptacles
Material	Composite
Material - Mounting Hardware	Mounting Screws
OEM Brand Name	Hubbell Bryant
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Response Time	5
Series	Specification Grade
Style	Surge Protection Only
Type	Duplex Receptacle
UPC	781786139015

Dimensions

Display Size	Standard
--------------	----------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Certifications and Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant D-2 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Power Disruption Solutions](#)
[Literature - General Literature - Duplex Surge Receptacles](#)
[Literature - General Literature - Surge Protection Devices](#)

Related Products

[SS26 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1\) GFCI Opening, Standard Size, Stainless Steel](#)
[SP52IGIA - Circuit Watch Surge Suppression Straight Blade Receptacle, Industrial/Commercial Grade, Isolated Ground, 15A 125V, 2- Pole 3-Wire Grounding, 5-15R](#)
[SP52IGOA - Circuit Watch Surge Suppression Straight Blade Receptacle, Industrial/Commercial Grade, Isolated Ground, 15A 125V, 2- Pole 3-Wire Grounding, 5-15R](#)
[SP52IGGYA - Circuit Watch Surge Suppression Straight Blade Receptacle, Industrial/Commercial Grade, Isolated Ground, 2- Pole 3-Wire Grounding, 15A 125V, 5-15R](#)
[SP52IGA - Circuit Watch Surge Suppression Straight Blade Receptacles, Duplex, Isolated Ground, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Blue](#)



A proud member of the Hubbell Family.