



# Circuit Watch Surge Suppression Straight Blade Receptacle, Industrial/Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, White

By Bryant  
Catalog # [SP52WA](#)



Circuit Watch Surge Suppression Straight Blade Receptacle,  
Industrial/Commercial Grade, 15A 125V, 2-Pole 3-Wire  
Grounding, 5-15R, White

## Application

Duplex with Light and Alarm

## General

Color	White
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED and Audible Alarm
Item Type	Surge Protection Receptacles
Material	Composite
Material - Mounting Hardware	Mounting Screws
OEM Brand Name	Hubbell Bryant
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Response Time	5
Series	Specification Grade
Style	Surge Protection Only
Type	Duplex Receptacle
UPC	781786139022

## Dimensions

Display Size	Standard
--------------	----------

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

## Certifications and Compliance

Nema Rating	5-15R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant D-2 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Power Disruption Solutions](#)  
[Literature - General Literature - Duplex Surge Receptacles](#)  
[Literature - General Literature - TRADESELECT RESIDENTIAL SELECTION GUIDE](#)  
[Literature - General Literature - tradeSELECT General Literature](#)  
[Literature - General Literature - Surge Protection Devices](#)

## Related Products

[SP521GA - Circuit Watch Surge Suppression Straight Blade Receptacles, Duplex, Isolated Ground, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Blue](#)  
[P26W - Wallplate, 1-Gang, 1\) Decorator, White](#)  
[SP52A - Circuit Watch Surge Suppression Straight Blade Receptacle, Industrial/Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brown](#)  
[SP521GWA - Circuit Watch Surge Suppression Straight Blade Receptacle, Industrial/Commercial Grade, Isolated Ground, 15A 125V, 2- Pole 3-Wire Grounding, 5-15R](#)  
[SP52GYA - Circuit Watch Surge Suppression Straight Blade Receptacle, Industrial/Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Gray](#)



A proud member of the Hubbell Family.