



Circuit Watch Surge Suppression Straight Blade Receptacle, Industrial/Commercial Grade, Isolated Ground, 20A 125V, 2- Pole 3-Wire Grounding, 5-20R

By Bryant
Catalog # [SP53IGA](#)

Circuit Watch Surge Suppression Straight Blade Receptacle,
Industrial/Commercial Grade, Isolated Ground, 20A 125V, 2-
Pole 3-Wire Grounding, 5-20R, Brown



Application

IG Duplex with Light and Alarm

General

| | |
|------------------------------|--|
| Color | Blue |
| EU RoHS Indicator | No |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Indicator(s) Type | LED and Audible Alarm |
| Item Type | Surge Protection Receptacles |
| Material | Composite |
| Material - Mounting Hardware | Mounting Screws |
| OEM Brand Name | Hubbell Bryant |
| Operating Temperature | 32 Deg F to 140 Deg F (0 Deg C to 60 Deg C) |
| Outlet | Straight Blade |
| Response Time | 5 |
| Series | Specification Grade |
| Style | Isolated Ground |
| Type | Duplex Receptacle |
| UPC | 781786139169 |

Dimensions

| | |
|--------------|----------|
| Display Size | Standard |
|--------------|----------|

Electrical Ratings

| | |
|----------------------------|-----------------|
| Amperage Rating | 20 A |
| Connectivity | Terminal Screws |
| Current / Amperage Rating | 20 A |
| Current Rating | 20 A |
| Frequency Rating | 60 Hz |
| Phase | Single Phase |
| Voltage Rating | 125 V |
| Voltage Rating Description | 125 V |

Certifications and Compliance

| | |
|-------------|-------|
| Nema Rating | 5-20R |
|-------------|-------|

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Catalog Page - Bryant D-2 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Power Disruption Solutions](#)
[Literature - General Literature - Duplex Surge Receptacles](#)
[Literature - General Literature - Surge Protection Devices](#)

Related Products

[SP53A - Circuit Watch Surge Suppression Straight Blade Receptacle, Industrial/Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Brown](#)
[SP53IGOA - Circuit Watch Surge Suppression Straight Blade Receptacle, Industrial/Commercial Grade, Isolated Ground, 20A 125V, 2- Pole 3-Wire Grounding, 5-20R](#)
[SP53IGGYA - Circuit Watch Surge Suppression Straight Blade Receptacle, Industrial/Commercial Grade, Isolated Ground, 20A 125V, 2- Pole 3-Wire Grounding, 5-20R](#)
[SP53GYA - Circuit Watch Surge Suppression Straight Blade Receptacle, Industrial/Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Gray](#)
[SS26 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1\) GFCI Opening, Standard Size, Stainless Steel](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-SP53IGA-SPEC-EN | REV 7/2023