



Circuit Watch Surge Suppression Straight Blade Receptacle, Industrial/Commercial Grade, Isolated Ground, 20A 125V, 5- 20R, White

By Bryant
Catalog # [SP53IGWA](#)

Circuit Watch Surge Suppression Straight Blade Receptacle,
Industrial/Commercial Grade, Isolated Ground, 20A 125V, 5-
20R, White



Application

IG Duplex with Light and Alarm

General

Color	White
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED and Audible Alarm
Item Type	Surge Protection Receptacles
Material	Composite
Material - Mounting Hardware	Mounting Screws
OEM Brand Name	Hubbell Bryant
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Response Time	5
Series	Specification Grade
Style	Isolated Ground
Type	Duplex Receptacle
UPC	781786139190

Dimensions

Display Size	Standard
--------------	----------

Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Certifications and Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant D-2 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Power Disruption Solutions](#)
[Literature - General Literature - Duplex Surge Receptacles](#)
[Literature - General Literature - Surge Protection Devices](#)

Related Products

[P26W - Wallplate, 1-Gang, 1\) Decorator, White](#)
[SP53WA - Circuit Watch Surge Suppression Straight Blade
Receptacle, Industrial/Commercial Grade, 20A 125V, 2-Pole 3-
Wire Grounding, 5-20R, White](#)
[SP53IGA - Circuit Watch Surge Suppression Straight Blade
Receptacle, Industrial/Commercial Grade, Isolated Ground,
20A 125V, 2- Pole 3-Wire Grounding, 5-20R](#)
[SP53A - Circuit Watch Surge Suppression Straight Blade
Receptacle, Industrial/Commercial Grade, 20A 125V, 2-Pole 3-
Wire Grounding, 5-20R, Brown](#)
[SP53IGGYA - Circuit Watch Surge Suppression Straight Blade
Receptacle, Industrial/Commercial Grade, Isolated Ground,
20A 125V, 2- Pole 3-Wire Grounding, 5-20R](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-SP53IGWA-SPEC-EN | REV 7/2023