



Wire and Cable Management, Support Grip, Single Eye, Split Mesh, Lace Closing, Stainless Steel, 1.25-1.49"

By Bryant
Catalog # SPS125US



Wire and Cable Management, Support Grip, Single Eye, Split Mesh, Lace Closing, Stainless Steel, 1.25-1.49"

Features

- Single Eye
- Split Mesh
- Lace Closing
- Stainless Steel
- 1.25-1.49"

Application

Single Eye

General

Approx Breaking Strength	4,490 lbs
Catalog Number	SPS125US
Construction	Woven
EU RoHS Indicator	No

Material	Stainless Steel
Material - Mounting Hardware	Screw Hook or Beam Clamp
OEM Brand Name	Hubbell Bryant
Series	Standard Duty
Style	Split Mesh, Lace Closing
Type	Single Eye
UPC	781786006546

Conductor Related

Cable Diameter Range	1.25 in-1.49 in
Cable Size	1.25-1.49" (3.17-3.78)

Product Assets

- [Catalog Page - BRY N-13 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - SPS125US](#)