




Wallplates and Boxes, Metallic Plates, 2- Gang, 1) Toggle 1) 1.40" Opening, Standard Size, Stainless Steel

By Bryant
Catalog # [SS17](#)

Wallplates and Boxes, Metallic Plates, 2- Gang, 1) Toggle 1) 1.40" Opening, Standard Size, Stainless Steel



Features

- Ideal for highly corrosive environments
- Non-magnetic
- Protective plastic film helps to prevent scratches and damage

Application

Protection against contact of live terminals and wiring.
Provides finished look to installation.

General

Construction	Stamped
Cutout	1) Toggle, 1) 1.40" Opening
EU RoHS Indicator	Yes
Item Type	Screw Mount
Material	Stainless Steel, Type 302/304
Material - Mounting Hardware	Screw Mounting
Number of Gang(s)	2-Gang
Orientation	Vertical Mount
Size	Standard
Style	1-Toggle, 1-Single Receptacle
Type	Combination
UPC	883778200762

Dimensions

Display Size	Standard Sized
Thickness	0.035

Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-SS17-SPEC-EN | REV 7/2023