BRYANT®

Wallplates and Boxes, Metallic Plates, 2- Gang, 2) GFCI Openings, 430 Stainless Steel

By Bryant Catalog # SS262L

Wallplates and Boxes, Metallic Plates, 2- Gang, 2) GFCI Openings, 430 Stainless Steel



Features

- Environments subjected to heavy abuse
- Ideal for highly corrosive environments
- Magnetic: 17.0% Chromium, Less than 0.5% Nickel
- Finish is lacquer coated to inhibit oxidation

Application

Protection against contact of live terminals and wiring. Provides finished look to installation.

General

Construction Stamped Cutout 2) Decorator

EU RoHS Indicator No

Item TypeDecorator WallplatesMaterialStainless Steel, Type 430

Material - Mounting Hardware Screw Mounting

Number of Gang(s) 2-Gang

Operating Temperature -40°Cto 85 °C
Orientation Vertical Mount
Size Standard
Style 2-Decorator
Type • Decorator
• Decorator

UPC 883778095108

Dimensions

Display Size Standard Sized

Thickness 0.035

Certifications and Compliance

Industry Standard(s) UL Listed

Logistics

Carton Quantity 10

Product Assets

Catalog Page - Wiring AA-12 Catalog Page Catalog Page - Bryant Q-5 Catalog page Catalogs - Bryant Full Line Catalog

Literature - General Literature - Stainless Steel Wallplates

