




Wallplates and Boxes, Metallic Plates, 2- Gang, 2) Toggle Openings, 430 Stainless Steel

By Bryant
Catalog # [SS2L](#)

Wallplates and Boxes, Metallic Plates, 2- Gang, 2) Toggle Openings, 430 Stainless Steel



Features

- Ideal for highly corrosive environments
- Non-Magnetic
- Protective plastic film helps to prevent scratches and damage

Application

Protection against contact of live terminals and wiring.
Provides finished look to installation.

General

Construction	Stamped
Cutout	2) Toggle
EU RoHS Indicator	No
Item Type	Toggle Switch Plate
Material	Stainless Steel, Type 430
Material - Mounting Hardware	Screw Mounting
Number of Gang(s)	2-Gang
Operating Temperature	-40°C to 85 °C
Orientation	Vertical Mount
Size	Standard
Style	2-Toggle
Type	<ul style="list-style-type: none">• Toggle• Toggle
UPC	883778095061

Dimensions

Display Size	Standard Sized
Thickness	0.035

Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant Q-6 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Stainless Steel Wallplates](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-SS2L-SPEC-EN | REV 7/2023