



Wallplates and Boxes, Metallic Plates, 1- Gang, 1) 1.60" Opening, Standard Size, Stainless Steel

By Bryant
Catalog # [SS720](#)

Twist-Lock® Devices, Wallplates, 1-Gang, Accessories for 20 and 30 Amp 3, 4 and 5 Wire Devices, Stainless steel 302/304, .035 in. (0.9), horizontal brushed finish



Features

- Used with Single Receptacles with Face Dia. 1.60" (40.6)

Application

Protection against contact of live terminals and wiring.
Provides finished look to installation.

General

Construction	Stamped
Cutout	1) 1.60" Opening
EU RoHS Indicator	Yes
Item Type	Wallplates, 1-Gang
Material	Stainless Steel
Material - Mounting Hardware	Screw Mounting
Number of Gang(s)	1-Gang
Operating Temperature	-40°C to 85 °C
Orientation	Vertical Mount
Size	1-Gang
Style	For 20A and 30A 3-5 Wire Devices
Type	<ul style="list-style-type: none">• Plates• Plates
UPC	883778201165

Dimensions

Display Size	Standard Sized
Thickness	0.035
Weight	0.1 lb

Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant Q-8 Catalog page](#)
[Catalog Page - Bryant Q-24 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-SS720-SPEC-EN | REV 7/2023