



Wallplates and Boxes, Metallic Plates, 1- Gang, 1) 2.15" Opening, Standard Size, Stainless Steel

By Bryant
Catalog # [SS723](#)

Wallplates and Boxes, Metallic Plates, 1- Gang, 1) 2.15" Opening, Standard Size, Stainless Steel.



Features

- Ideal for highly corrosive environments
- Non-magnetic
- Protective plastic film helps to prevent scratches and damage

Application

Protection against contact of live terminals and wiring.
Provides finished look to installation.

General

Construction	Stamped
Cutout	1) 2.15" Opening, 2-Bolt
EU RoHS Indicator	Yes
Item Type	Screw Mount
Material	Stainless Steel, Type 302/304
Material - Mounting Hardware	Screw Mounting
Number of Gang(s)	1-Gang
Operating Temperature	-40°C to 85 °C
Orientation	Vertical Mount
Size	Standard
Style	1-Single - 2.16 in Hole
Type	<ul style="list-style-type: none">• Single• Single
UPC	883778201172

Dimensions

Display Size	Standard Sized
Thickness	0.04
Weight	0.1 lb

Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant Q-8 Catalog page](#)
[Catalog Page - Bryant Q-24 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Stainless Steel Wallplates](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-SS723-SPEC-EN | REV 7/2023