



## Wallplates and Boxes, Metallic Plates, 1- Gang, 1) 1.70" Opening, Standard Size, Stainless Steel

By Bryant  
Catalog # [SS725](#)

Twist-Lock® Devices, Receptacle Wallplates, Stainless steel  
302/304, .035 in. (0.9), horizontal brushed finish



### Features

- Used with Single Receptacles with Face Dia. 1.74" (44.2)

### Application

Protection against contact of live terminals and wiring.  
Provides finished look to installation.

### General

Construction	Stamped
Cutout	1) 1.70" Opening
EU RoHS Indicator	Yes
Item Type	Receptacle Wallplates
Material	Stainless Steel, Type 302/304
Material - Mounting Hardware	Screw Mounting
Number of Gang(s)	1-Gang
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Orientation	Vertical Mount
Size	Standard
Style	1-Single - 1.74 in. Hole
Type	<ul style="list-style-type: none"><li>• Single</li><li>• Single</li></ul>
UPC	883778201189

### Dimensions

Display Size	Standard Sized
Thickness	0.035
Weight	0.1 lb

### Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog Page - Bryant Q-8 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-SS725-SPEC-EN | REV 7/2023