



Wallplates and Boxes, Metallic Plates, 1- Gang, 1) 1.937" Openings, Standard Size, Stainless Steel

By Bryant
Catalog # [SS737](#)

Twist-Lock® Devices, 30 Amp Hubbellock® Accessories,
Receptacle Wallplates, 302/304 stainless, single gang,
smooth. NOT weatherproof.



Features

- Ideal for highly corrosive environments
- Non-magnetic
- Protective plastic film helps to prevent scratches and damage

Application

Designed for highly corrosive environments

General

Construction	Stamped
Cutout	1) 1.937" Opening
EU RoHS Indicator	Yes
Environmental Conditions	Corrosion Resistant
Item Type	Single Receptacle Wallplate
Material	Stainless Steel, Type 302/304
Material - Mounting Hardware	Screw Mounting
Number of Gang(s)	1-Gang
Orientation	Vertical Mount
Size	Standard
Style	1-Single - 1.97 in Hole
Type	Single
UPC	883778201196

Dimensions

Display Size	Standard Sized
Thickness	0.035
Weight	0.65 lb

Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant Q-8 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-SS737-SPEC-EN | REV 7/2023