



## Wallplates and Boxes, Metallic Plates, 1- Gang, 1) Toggle Opening, 430 Stainless Steel

By Bryant  
Catalog # [SS8L](#)

Twist-Lock® Devices, Wallplates, 1-Gang, Accessories for 15  
Amp 2 and 3 Wire Devices, Stainless steel 430, .035 in. (0.9),  
horizontal brushed finish



### Features

- Used with Duplex Receptacles

### Application

Protection against contact of live terminals and wiring.  
Provides finished look to installation.

### General

Construction	Stamped
Cutout	1) Duplex
EU RoHS Indicator	No
Item Type	Wallplates, 1-Gang
Material	Stainless Steel, Type 430
Material - Mounting Hardware	Screw Mounting
Number of Gang(s)	1-Gang
Operating Temperature	-40°C to 85 °C
Orientation	Vertical Mount
Size	Standard
Style	1-Duplex
Type	<ul style="list-style-type: none"><li>• Duplex</li><li>• Duplex</li></ul>
UPC	883778095160

### Dimensions

Display Size	Standard Sized
Thickness	0.035

### Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog Page - Bryant Q-7 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Stainless Steel Wallplates](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-SS8L-SPEC-EN | REV 7/2023