



Bryant, Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, .50-.61" Cable Range

By Bryant
Catalog # [SSR050](#)

Bryant, Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, .50-.61" Cable Range



Application

General Cable Pulling

General

Approx Breaking Strength	1,500 lbs
Construction	Woven
Load Capacity	300
Material	Steel, Galvanized
Material - Mounting Hardware	Non-Mounted
OEM Brand Name	Hubbell Bryant
Series	Slack Grip
Style	Split Mesh, Rod Closing, Single Weave
Type	Offset Eye
UPC	781786271685

Conductor Related

Cable Diameter Range	0.50 in-0.61 in
Cable Size	.50-.61" (1.27-1.55)
Cable Specification	UL Listed Circuit Wire

Product Assets

[Catalog Page - Bryant N-7 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Wiring_WLFVM032](#)
[Literature - Wiring_WLBVM044](#)
[Literature - Pulp & Paper Solutions](#)

Related Products

[SCD075 - Bryant, Wire and Cable Management, Pulling Grip, Slack Mesh, Single Eye, .75-.99" Cable Range](#)
[SCD100 - Bryant, Wire and Cable Management, Pulling Grip, Slack Mesh, Single Eye, 1.00-1.24" Cable Range](#)
[SSR075 - Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, .75-.99" Cable Range](#)
[SSR100 - Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, 1.00-1.24" Cable Range](#)
[SSR062 - Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, .62-.74" Cable Range](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-SSR050-SPEC-EN | REV 7/2023