



# Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, .62-.74" Cable Range

By Bryant  
Catalog # [SSR062](#)

Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, .62-.74" Cable Range



## Application

General Cable Pulling

## General

Approx Breaking Strength	1,800 lbs
Construction	Woven
Load Capacity	360
Material	Steel, Galvanized
Material - Mounting Hardware	Non-Mounted
OEM Brand Name	Hubbell Bryant
Series	Slack Grip
Style	Split Mesh, Rod Closing, Single Weave
Type	Offset Eye
UPC	781786271708

## Conductor Related

Cable Diameter Range	0.62 in-0.74 in
Cable Size	.62-.74" (1.57-1.88)
Cable Specification	UL Listed Circuit Wire

## Product Assets

[Catalog Page - Bryant N-7 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - WIRING\\_WLFVM034](#)  
[Literature - Wiring\\_WLFVM032](#)  
[Literature - Wiring\\_WLBVM044](#)  
[Literature - Pulp & Paper Solutions](#)

## Related Products

[SCD075 - Bryant, Wire and Cable Management, Pulling Grip, Slack Mesh, Single Eye, .75-.99" Cable Range](#)  
[SSR050 - Bryant, Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, .50-.61" Cable Range](#)  
[SSR075 - Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, .75-.99" Cable Range](#)  
[SCD100 - Bryant, Wire and Cable Management, Pulling Grip, Slack Mesh, Single Eye, 1.00-1.24" Cable Range](#)  
[SSR100 - Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, 1.00-1.24" Cable Range](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-SSR062-SPEC-EN | REV 7/2023