



Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, 1.00-1.24" Cable Range

By Bryant
Catalog # SSR100



Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, 1.00-1.24" Cable Range

Application

General Cable Pulling

General

Approx Breaking Strength	3,400 lbs
Catalog Number	SSR100
Construction	Woven
EU RoHS Indicator	Yes
Load Capacity	680
Material	Steel, Galvanized
Material - Mounting Hardware	Non-Mounted
OEM Brand Name	Hubbell Bryant
Series	Slack Grip

Style

Split Mesh, Rod Closing, Single Weave

Type
UPC

Offset Eye
781786271746

Conductor Related

Cable Diameter Range	1.00-1.24 in
Cable Size	1.00-1.24" (2.54-3.15)
Cable Specification	UL Listed Circuit Wire

Product Assets

[Catalog Page - BRY N-7 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - SSR100](#)