



# Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, 1.25-1.49" Cable Range

By Bryant  
Catalog # SSR125



Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, 1.25-1.49" Cable Range

## Application

General Cable Pulling

## General

Approx Breaking Strength	4,500 lbs
Catalog Number	SSR125
Construction	Woven
EU RoHS Indicator	Yes
Load Capacity	900
Material	Steel, Galvanized
Material - Mounting Hardware	Non-Mounted
OEM Brand Name	Hubbell Bryant
Series	Slack Grip

Style

Split Mesh, Rod Closing, Single Weave

Type  
UPC

Offset Eye  
781786271760

## Conductor Related

Cable Diameter Range	1.25 in-1.49 in
Cable Size	1.25-1.49" (3.17-3.78)
Cable Specification	UL Listed Circuit Wire

## Product Assets

- [Catalog Page - BRY N-7 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - SSR125](#)