



Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, 1.50-1.74" Cable Range

By Bryant
Catalog # SSR150

Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, 1.50-1.74" Cable Range



Application

General Cable Pulling

General

Approx Breaking Strength	5,800 lbs
Construction	Woven
Load Capacity	1160
Material	Steel, Galvanized
Material - Mounting Hardware	Non-Mounted
OEM Brand Name	Hubbell Bryant
Series	Slack Grip
Style	Split Mesh, Rod Closing, Single Weave
Type	Offset Eye
UPC	781786271784

Conductor Related

Cable Diameter Range	1.50 in-1.74 in
Cable Size	1.50-1.74" (3.81-4.42)
Cable Specification	UL Listed Circuit Wire

Product Assets

[Catalog Page - Bryant N-7 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[SSR125 - Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, 1.25-1.49" Cable Range](#)
[SSR175 - Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, 1.75-1.99" Cable Range](#)
[SCD175 - Bryant, Wire and Cable Management, Pulling Grip, Slack Mesh, Single Eye, 1.75-1.99" Cable Range](#)
[SCD200 - Bryant, Wire and Cable Management, Pulling Grip, Slack Mesh, Single Eye, 2.00-2.49" Cable Range](#)
[SSR200 - Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, 2.00-2.49" Cable Range](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-SSR150-SPEC-EN | REV 7/2023