



# Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, 2.50-2.99" Cable Range

By Bryant  
Catalog # [SSR250](#)

Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, 2.50-2.99" Cable Range



## Application

General Cable Pulling

## General

Approx Breaking Strength	11,000 lbs
Construction	Woven
Load Capacity	2200
Material	Steel, Galvanized
Material - Mounting Hardware	Non-Mounted
OEM Brand Name	Hubbell Bryant
Series	Slack Grip
Style	Split Mesh, Rod Closing, Single Weave
Type	Offset Eye
UPC	781786271845

## Conductor Related

Cable Diameter Range	2.50 in-2.99 in
Cable Size	2.50-2.99" (6.35-7.59)
Cable Specification	UL Listed Circuit Wire

## Product Assets

[Catalog Page - Bryant N-7 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

[SSR350 - Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, 3.50-3.99" Cable Range](#)  
[SSR200 - Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, 2.00-2.49" Cable Range](#)  
[SCD350 - Bryant, Wire and Cable Management, Pulling Grip, Slack Mesh, Single Eye, 3.50-3.99" Cable Range](#)  
[SSR300 - Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, 3.00-3.49" Cable Range](#)  
[SCD300 - Bryant, Wire and Cable Management, Pulling Grip, Slack Mesh, Single Eye, 3.00-3.49" Cable Range](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-SSR250-SPEC-EN | REV 7/2023