



Straight Blade Devices, Receptacle Cordsets, Receptacle with Pilot Light, Commercial/Industrial, 15A 125V, 2-Pole 3- Wire Grounding, 5-15R, 6' Cord



By Bryant
Catalog # T1254GF6

Straight Blade Devices, Receptacle Cordsets, Receptacle with Pilot Light, Commercial/Industrial, 15A 125V, 2-Pole 3- Wire Grounding, 5-15R, 6' Cord, Yellow, Single Pack

Application

Commercial/Industrial

General

Color	Yellow
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Quad-Plex Cord Set
Material	Composite
Material - Mounting Hardware	Screw Mounting
OEM Brand Name	Hubbell Bryant
Series	Commercial
Style	Cord Sets
Type	Four Outlet Receptacle
UPC	781786181007

Dimensions

Display Size	Standard Sized Product
Weight	1.7 lb

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	120 V
Voltage Rating Description	120 V
Wattage	1875

Conductor Related

Wire Size	#14 AWG to #12 AWG
-----------	--------------------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalog Page - Bryant A-15 Catalog page](#)
- [Catalog Page - Bryant C-8 Catalog page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - General Literature - Power Disruption Solutions](#)
- [Literature - General Literature - Ground Fault Receptacles](#)
- [Literature - General Literature - GFCI Portable Plug](#)



A proud member of the Hubbell Family.