



# Straight Blade Devices, Receptacle Cordsets, TVSS Receptacle, Commercial/Industrial, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, 6' Cord

By Bryant  
Catalog # [T1254SI6A](#)



Straight Blade Devices, Receptacle Cordsets, TVSS Receptacle, Commercial/Industrial, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, 6' Cord, Ivory, Single Pack

## Application

Commercial/Industrial

## General

Color	Ivory
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Quad-Plex Cord Set
Material	Composite
Material - Mounting Hardware	Screw Mounting
OEM Brand Name	Hubbell Bryant
Series	Quadplex®
Style	Cord Sets
Type	Non-Metallic
UPC	781786191006

## Dimensions

Display Size	Standard Sized Product
Weight	1.45 lb

## Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

## Conductor Related

Wire Size	#14 AWG to #12 AWG
-----------	--------------------

## Logistics

Carton Quantity	5
-----------------	---

## Product Assets

[Catalog Page - Bryant B-5 Catalog page](#)  
[Catalog Page - Bryant A-15 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Power Disruption Solutions](#)

## Related Products

[BRY7PS1050M - Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 7\) Receptacles, Metallic Body, 1050 Joules, 6' Cord, Modem Protection](#)  
[BRY6MPS1050 - Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 6\) Receptacles, Metallic Body, 1050 Joules, 6' Cord](#)  
[T1254SI6A - Straight Blade Devices, Receptacle Cordsets, TVSS Receptacle, Commercial/Industrial, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, 6' Cord](#)  
[BRY8PS2100D - Bryant Wiring Devices, Cord and Cable Reels, Commercial Cord Reel, 25'With HBL5969VBLK Connector Body, Yellow.](#)  
[BRY6MPS - Straight Blade Devices, Plug Strip, 6\) Receptacles, Metallic Body, 6' Cord](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-T1254SI6A-SPEC-EN | REV 7/2023