



Temporary Power Products, Distribution Boxes, Cable Sets and Receptacles, Cable, 100A Yellow, Molded-On, 100'

By Bryant
Catalog # [TPC50B](#)



Temporary Power Products, Distribution Boxes, Cable Sets and
Receptacles, Cable, 100A Yellow, Molded-On, 100'

Application

Power Cables

General

Color	Yellow
EU RoHS Indicator	No
Environmental Conditions	Indoor and Outdoor
Item Type	Factory Terminated Devices
Jacket	PVC
OEM Brand Name	Hubbell Bryant
Series	Cable Set
Type	Cord Set
UPC	781786141476

Electrical Ratings

Current / Amperage Rating	50 A
Current Rating	50 A
Phase	Single Phase
Voltage Rating	125/250 VAC
Wattage	12500

Conductor Related

Cord Length	600
-------------	-----

Product Assets

[Catalog Page - Bryant C-11 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Watertight Wiring Devices](#)
[Literature - General Literature - Cam-Type Devices and Power Distribution Boxes](#)

Related Products

[RW51470 - Wallplates and Boxes, Weatherproof Covers, 1-Gang, Duplex Opening, Vertical, Gray](#)
[CRS20 - Straight Blade Devices, Receptacles, Duplex, Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Brown, Single Pack](#)
[7420B - Wallplates and Boxes, Weatherproof Covers, 1- Gang, 1\) 1.62" Opening, Standard Size, Cast Aluminum](#)
[CS6364L - Locking Devices, Twist-Lock®, Economy, Female Connector Body, 50A125/250V, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black](#)
[7780 - Wallplates and Boxes, Weatherproof Covers, 1- Gang, 1\) 50A Locking Opening, Standard Size, Black Polycarbonate](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-TPC50B-SPEC-EN | REV 7/2023