



Temporary Power Products, Distribution Boxes, Complete Unit, Locking Style, 50A 125/250V, Yellow

By Bryant
Catalog # [TPDLB](#)



Temporary Power Products, Distribution Boxes, Complete Unit,
Locking Style, 50A 125/250V, Yellow

Application

Portable/Temporary

General

Color	Yellow
EU RoHS Indicator	No
Environmental Conditions	Indoor and Outdoor
Item Type	Unit with Locking Devices
Material	Composite
Material - Mounting Hardware	Free Standing
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Series	Distribution Box
Type	Twist-Lock®
UPC	781786141469

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Connectivity	Plug-In
Current / Amperage Rating	50 A
Current Rating	50 A
Phase	Single Phase
Voltage Rating	120/240 VAC
Wattage	12500

Conductor Related

Number Of Wires	4-Wire Grounding
Wire Size	Pre-Wired

Certifications and Compliance

Nema Rating	Muli Outlet
-------------	-------------

Product Assets

[Catalog Page - Bryant C-11 Catalog page](#)
[Catalog Page - Bryant L-10 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Watertight Wiring Devices](#)
[Literature - General Literature - Cam-Type Devices and Power Distribution Boxes](#)

Related Products

[CS6369L - Locking Devices, Twist-Lock®, Economy, Receptacle, 50A 125/250V, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black](#)
[7780 - Wallplates and Boxes, Weatherproof Covers, 1- Gang, 1\) 50A Locking Opening, Standard Size, Black Polycarbonate](#)
[7420B - Wallplates and Boxes, Weatherproof Covers, 1- Gang, 1\) 1.62" Opening, Standard Size, Cast Aluminum](#)
[CS6364L - Locking Devices, Twist-Lock®, Economy, Female Connector Body, 50A125/250V, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black](#)
[CS6365L - Locking Devices, Twist-Lock®, Economy, Male Plug, 50A 125/250V, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-TPDLB-SPEC-EN | REV 7/2023