



USB Charger Hospital Grade Receptacle, 20A 125V Duplex, Power Delivery 55W Type C Ports, NEMA 5-20R, White

By Bryant
Catalog # USB8300CPDW



Tamper Resistant Hospital Grade Receptacle, 2-Pole 3-Wire Grounding, 1 Type "C" Power Delivery, 1 Type "C" Standard 5V

Features

- High Power 55 Watt USB Power Delivery 3.0 Standard, 5 Volt USB BC1.2 Output
- Two Type C USB Ports, One Supports Power Delivery
- Tamper Resistant Hospital Grade Duplex Compatible
- USB Ports Rated 10,000 Cycles

General

Catalog Number	USB8300CPDW
Color	White
Number Of Poles	2-Pole
Series	Hospital Grade USB Charger
Style	Style Line Decorator
Type	Tamper Resistant USB
UPC	783585723402

Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating	125 V

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications And Compliance

Industry Standard(s)	NEMA 5-20R, USB PD 3.0, USB BC1.2
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Installation Manuals - PD3040](#)
- [Literature - FREQUENTLY ANSWERED QUESTIONS USB-C Power Delivery Receptacles](#)
- [Sales Drawings - M-14671](#)
- [Specifications - USB8300CPDW](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Hubbell USB-C PD Receptacles](#)