



2-Port USB Charger with Single Pole/Three Way Switch, 3A 5V, 15A 125V, Ivory

By Bryant
Catalog # [USBB102I](#)

2-Port USB Charger with Single Pole/Three Way Switch, 3A 5V, 15A 125V, Ivory



Application

Side Wire

General

Color	Ivory
Series	Switch with USB Ports
Style	(1) Single Pole (2) USB Ports
Type	Rocker/Decorator
UPC	781786193659

Electrical Ratings

Amperage Rating	15/3 A
Current / Amperage Rating	15/3 A
Voltage Rating	120 VAC / 5 VDC
Voltage Rating Description	120 VAC / 5 VDC

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - Bryant E-7 Catalog page](#)
[Catalog Page - Bryant A-17 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[USBB15A5 - USB Charger Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, 2\) 5A USB Ports, Brown](#)
[P26I - Wallplate, 1-Gang, 1\) Decorator, Ivory](#)
[USBB15A5W - USB Charger Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, 2\) 5A USB Ports, White](#)
[USBB102LA - 2-Port USB Charger with Single Pole/Three Way Switch, 3A 5V, 15A 125V, Light Almond](#)
[USBB102BK - 2-Port USB Charger with Single Pole/Three Way Switch, 3A 5V, 15A 125V, Black](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-USBB102I-SPEC-EN | REV 7/2023