



# 15A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type A & C USB Ports, Gray

By Bryant  
Catalog # [USBB15AC5GYWR](#)

15A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type A & C USB Ports, Gray



## General

UPC 781786917439

## Electrical Ratings

Current / Amperage Rating 15 A

## Logistics

Carton Quantity 10

## Product Assets

[Catalog Page - Bryant A-17 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

[P26GY - Wallplate, 1-Gang, 1\) Decorator, Gray](#)  
[USBB15AC5IWR - 15A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type A & C USB Ports, Ivory](#)  
[USBB15AC5WWR - 15A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type A & C USB Ports, White](#)  
[USBB15AC5BKWR - 15A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type A & C USB Ports, Black](#)  
[USBB15AC5LAWR - 15A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type A & C USB Ports, Light Almond](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-USBB15AC5GYWR-SPEC-EN | REV 7/2023