



15A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type A & C USB Ports, Brown

By Bryant
Catalog # [USBB15AC5WR](#)

15A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type A & C USB Ports, Brown



General

UPC 781786917477

Electrical Ratings

Current / Amperage Rating 15 A

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - Bryant A-17 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[USBB15AC5IWR - 15A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type A & C USB Ports, Ivory](#)
[USBB15AC5BKWR - 15A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type A & C USB Ports, Black](#)
[USBB15AC5WWR - 15A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type A & C USB Ports, White](#)
[USBB15AC5LAWR - 15A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type A & C USB Ports, Light Almond](#)
[P26 - Wallplate, 1-Gang, 1\) Decorator, Brown](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-USBB15AC5WR-SPEC-EN | REV 7/2023