



15A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type C USB Port, Black

By Bryant
Catalog # [USBB15C5BKWR](#)

15A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type C USB Port, Black



General

Color	Black
Number Of Poles	2
Series	USB Charger
Style	Style Line Decorator
Type	Two Type-C USB Ports

Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3
-----------------	---

Certifications and Compliance

Nema Rating	5-15R
-------------	-------

Product Assets

Related Products

- [P26BK - Wallplate, 1-Gang, 1\) Decorator, Black](#)
- [USBB15C5WWR - 15A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type C USB Port, White](#)
- [USBB15C5LAWR - 15A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type C USB Port, Light Almond](#)
- [USBB15C5GYWR - 15A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type C USB Port, Gray](#)
- [USBB15C5IWR - 15A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type C USB Port, Ivory](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-USBB15C5BKWR-SPEC-EN | REV 7/2023