



# Straight Blade Devices, Receptacles, Duplex, USB Charger, 5V 3A, 2-Port, 15A 125V, 2-Pole 3- Wire Grounding, 5-15R, LightAlmond

By Bryant  
Catalog # [USBB15LA](#)



Straight Blade Devices, Receptacles, Duplex, USB Charger, 5V 3A, 2-Port, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, LightAlmond

## Application

Commercial Specification Grade

## General

Color	Light Almond
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Decorator Duplex
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Standard
Style	Decorator
Type	Duplex Receptacle
UPC	781786193284

## Dimensions

Display Size	Standard Sized
--------------	----------------

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

## Certifications and Compliance

Nema Rating	5-15R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Literature - General Literature - USB Device Charging Centers Literature](#) - [General Literature - tradeSELECT General Literature](#)

## Related Products

- [USBB15AC - USB Charger Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding](#)
- [USBB15ACW - USB Charger Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding](#)
- [USBB15ACGY - USB Charger Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding](#)
- [P26LA - Wallplate, 1-Gang, 1\) Decorator, Light Almond](#)
- [USBB15ACLA - USB Charger Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding](#)



A proud member of the Hubbell Family.