



Straight Blade Devices, Receptacles, Duplex, USB Charger, 5V 3A, 2-Port, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, White

By Bryant
Catalog # [USBB15W](#)

Straight Blade Devices, Receptacles, Duplex, USB Charger, 5V 3A, 2-Port, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, White



Application

Commercial Specification Grade

General

Color	White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Decorator Duplex
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Standard
Style	Decorator
Type	Duplex Receptacle
UPC	781786193260

Dimensions

Display Size	Standard Sized
--------------	----------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications and Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Literature - General Literature - USB Device Charging Centers](#)
[Literature - General Literature - tradeSELECT General Literature](#)

Related Products

[USBB15ACLA - USB Charger Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding](#)
[USBB15ACBK - USB Charger Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding](#)
[P26W - Wallplate, 1-Gang, 1\) Decorator, White](#)
[USBB15ACI - USB Charger Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding](#)
[USBB15AC - USB Charger Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-USBB15W-SPEC-EN | REV 7/2023