



20A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type A & C USB Ports, Black

By Bryant
Catalog # [USBB20AC5BKWR](#)

20A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type A & C USB Ports, Black



General

UPC 781786917491

Electrical Ratings

Current / Amperage Rating 20 A

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - Bryant A-17 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[USBB20AC5GYWR - 20A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type A & C USB Ports, Gray](#)
[USBB20AC5WWR - 20A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type A & C USB Ports, White](#)
[USBB20AC5IWR - 20A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type A & C USB Ports, Ivory](#)
[P26BK - Wallplate, 1-Gang, 1\) Decorator, Black](#)
[USBB20AC5WR - 20A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type A & C USB Ports, Brown](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-USBB20AC5BKWR-SPEC-EN | REV 7/2023