



## 20A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type A & C USB Ports, Gray

By Bryant  
Catalog # [USBB20AC5GYWR](#)

20A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type A & C USB Ports, Gray



### General

UPC 781786917514

### Electrical Ratings

Current / Amperage Rating 20 A

### Logistics

Carton Quantity 10

### Product Assets

[Catalog Page - Bryant A-17 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

### Related Products

[USBB20AC5BKWR - 20A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type A & C USB Ports, Black](#)  
[USBB20AC5WR - 20A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type A & C USB Ports, Brown](#)  
[USBB20AC5WWR - 20A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type A & C USB Ports, White](#)  
[USBB20AC5IWR - 20A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type A & C USB Ports, Ivory](#)  
[USBB20AC5LAWR - 20A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type A & C USB Ports, Light Almond](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-USBB20AC5GYWR-SPEC-EN | REV 7/2023