



15A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type C USB Port, Light Almond

By Bryant
Catalog # [USBB20C5LAWR](#)

15A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type C USB Port, Light Almond



General

Color	Light Almond
Number Of Poles	2
Series	USB Charger
Style	Style Line Decorator
Type	Two Type-C USB Ports

Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3
-----------------	---

Certifications and Compliance

Nema Rating	5-20R
-------------	-------

Product Assets

Related Products

[USBB20C5IWR](#) - 15A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type C USB Port, Ivory
[USBB20C5WWR](#) - 15A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type C USB Port, White
[USBB20C5GYWR](#) - 15A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type C USB Port, Gray
[USBB20C5BKWR](#) - 15A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type C USB Port, Black
[P26LA](#) - Wallplate, 1-Gang, 1) Decorator, Light Almond



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-USBB20C5LAWR-SPEC-EN | REV 7/2023