



Straight Blade Devices, Receptacles, Duplex, USB Charger, 5V 3A, 2-Port, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory

By Bryant
Catalog # USBB20I



Straight Blade Devices, Receptacles, Duplex, USB Charger, 5V 3A, 2-Port, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory

Features

- Duplex
- USB Charger
- 5V 3A
- 2-Port
- 20A 125V

Application

Commercial Specification Grade

General

| | |
|------------------------------|---|
| Catalog Number | USBB20I |
| Color | Ivory |
| EU RoHS Indicator | No |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Item Type | Decorator Duplex |
| Material | Thermoplastic |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 2-Pole |
| OEM Brand Name | Hubbell Bryant |
| Series | Standard |
| Style | Decorator |
| Type | Duplex Receptacle |
| UPC | 781786193338 |

Dimensions

Display Size Standard Sized Product

Electrical Ratings

| | |
|----------------------------|---------------------|
| Amperage Rating | 20 A |
| Connectivity | Back and Side Wired |
| Current / Amperage Rating | 20 A |
| Current Rating | 20 A |
| Phase | Single Phase |
| Voltage Rating | 125 V |
| Voltage Rating Description | 125 V |
| Wattage | 2500 |

Conductor Related

| | |
|-----------------|--------------------|
| Number Of Wires | 3-Wire |
| Wire Size | #14 AWG to #12 AWG |

Certifications And Compliance

| | |
|-------------|-------|
| Nema Rating | 5-20R |
|-------------|-------|

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Literature - General Literature - tradeSELECT General Literature](#)
[Literature - General Literature - USB Device Charging Centers](#)
[Specifications - USBB20I](#)