



## Patch Cord, AV, 8-Pin, Non-Plenum, Black, 100'

By Bryant  
Catalog # [VGA6100BK](#)

Patch Cord, AV, 8-Pin, Non-Plenum, Black, 100'



### Application

Horizontal Cable W/Male Ends

### General

Boot Type	None
EU RoHS Indicator	Yes
Item Type	X-END AV Plug-n-Play System
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	VGA
Temperature Rating	Per TIA
Type	VGA, Plug-n-Play
UPC	662620286891

### Dimensions

Outside Diameter	0.375
------------------	-------

### Electrical Ratings

Voltage Rating	600V AC kV
----------------	------------

### Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#28 AWG

### Logistics

Carton Quantity	5
-----------------	---

### Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-VGA6100BK-SPEC-EN | REV 7/2023