



Patch Cord, AV, 8-Pin, Plenum, Black, 25'

By Bryant
Catalog # [VGA6P25BK](#)



Patch Cord, AV, 8-Pin, Plenum, Black, 25'

Application

Horizontal Cable W/Male Ends

General

Boot Type	None
EU RoHS Indicator	Yes
Item Type	X-END AV Plug-n-Play System
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	VGA
Temperature Rating	Per TIA
Type	VGA, Plug-n-Play
UPC	662620286945

Dimensions

Outside Diameter	0.375
------------------	-------

Electrical Ratings

Voltage Rating	600V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#28 AWG

Logistics

Carton Quantity	20
-----------------	----

Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-VGA6P25BK-SPEC-EN | REV 7/2023