



## XLR Connector, Solder Type, Panel Mount, 3-Pin, 10 Pack

By Bryant  
Catalog # [XLR10](#)

XLR Connector, Solder Type, Panel Mount, 3-Pin, 10 Pack



### Application

D-Style XLR 3-Pole Locking Connection

### General

Contact	Beryllium Copper
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	iSTATION Pro Audio D-Style Connections
Material - Mounting Hardware	Snap-On- Snap-Fit
Temperature Rating	Per TIA
Type	XLR
UPC	662620285412

### Dimensions

Display Size	Standard Sized Product
--------------	------------------------

### Electrical Ratings

Connectivity	Solder
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

### Logistics

Carton Quantity	5
-----------------	---

### Product Assets

[Catalog Page - Bryant R-17 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

### Related Products

[USB10 - Connectors, USB Feed Thru, Panel Mount, 10 Pack](#)  
[IMAVB15W - iStation Module, Audio/Video, Unloaded, 1.5-Unit, White, 10 Pack](#)  
[IMAVB15GY - iStation Module, Audio/Video, Unloaded, 1.5-Unit, Gray, 10 Pack](#)  
[XLRST10 - XLR Connector, Screw Terminal, Panel Mount, 3-Pin, 10 Pack](#)  
[IMAVB15EI - iStation Module, Audio/Video, Unloaded, 1.5-Unit, Electric Ivory, 10 Pack](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-XLR10-SPEC-EN | REV 7/2023