

IEC Pin and Sleeve

32 A, 380-480 VAC, 3-POLE, 4-WIRE

Receptacle



- Features
- IP67 environmental ratings
  - Impact and corrosion resistant insulated non-metallic housing
  - Sequential contact engagement to prevent a momentary over-voltage
  - Color coded housings provide quick identification of mating devices


Ordering Information				
Description	Series	Color	UPC Number	Catalog Number
Heavy Duty Products, IEC Pin and Sleeve	Watertight IP67	Red	781786782679	BRY432R3W

Listings

VDE, CE

Specifications	
Application	High Ampacity Connections
Connection	Screwless Spring
Wire Size	#10AWG to #8AWG
Material	PBT
Mounting	Screw Mount

Performance	
<b>Electrical</b>	
Dielectric Voltage	Withstand 3000V AC
Max. Working Voltage	600V AC RMS
<b>Mechanical</b>	
Impact Resistance	Per CSA C22.2 No. 182.1 / UL1682
Product Identification	Identification and ratings are marked on device housing
Terminal Identification	Terminals identified in accordance with North American and IEC conventions
<b>Environmental</b>	
Flammability	HB
Ingress Protection	IP67
Moisture Resistance	IEC 60309-1
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.



Complementary Products

Complementary Products      Adapter Plate, Back Box

Online Resources

Customer Sales Drawings  
eCatalog

