

**Lighting Controls Residential / Light Commercial Rocker
Dimmer Switch**

0-10V LED, Three Way

Single Pole, 10A 120VAC, 5A 277 VAC

BRYANT®

Features

- Control for 0-10V LED loads only
- Trim Adjustment for Fine Tuning
- Digital Circuit Controlled
- Decorator Rocker Styling
- UL/cUL listed



Ordering Information

Description	Color	UPC	Catalog Number
Low Voltage Decorator Rocker Dimmer, 0-10V LED 10 A	Ivory	783585565798	LCD0108DI

Online Resources

[eCatalog](#)

Listings

UL/cUL listed

Specifications

Input Voltage	120V / 60Hz, 277V 60Hz
Lamp Type	0-10 V LED Lamps with or without Ballast, Forward Phase Cut
Wiring Type	Leads
Number of Poles	3 Pole, 4 Wire
Height	4.25 in.
Depth	2.0 in.
Width	2.5 in.
Weight	0.20 lbs.

BRYANT®