

## Lighting Controls Residential / Light Commercial Rocker Dimmer Switch

0-10V LED, Three Way

Single Pole, 10A 120VAC, 5A 277 VAC

# BRYANT®

### Features

- Control for 0-10V LED loads only
- Trim Adjustment for Fine Tuning
- Digital Circuit Controlled
- Decorator Rocker Styling
- UL/cUL listed



### Ordering Information

Description	Color	UPC	Catalog Number
Low Voltage Decorator Rocker Dimmer, 0-10V LED 10 A	White	783585565774	LCD0108DW

### Online Resources

[eCatalog](#)

### Listings

UL/cUL listed

### Specifications

Input Voltage	120V / 60Hz, 277V 60Hz
Lamp Type	0-10 V LED Lamps with or without Ballast, Forward Phase Cut
Wiring Type	Leads
Number of Poles	3 Pole, 4 Wire
Height	4.25 in.
Depth	2.0 in.
Width	2.5 in.
Weight	0.20 lbs.

# BRYANT®