

## Lighting Controls Residential / Light Commercial Slide Dimmer Switch

0-10V LED, Three Way

Single Pole, 10A 120VAC, 5A 277 VAC

# BRYANT®

### Features

- Control for 0-10V LED loads only
- Trim Adjustment for Fine Tuning
- Digital Circuit Controlled
- Decorator Slide Styling
- UL/cUL listed



### Ordering Information

| Description  | Color | UPC          | Catalog Number |
|--|-------|--------------|----------------|
| Low Voltage Decorator Slide Dimmer, 0-10V LED 10 A | White | 783585565804 | LCD0108SW      |

### Online Resources

[eCatalog](#)

### Listings

UL/cUL listed

### Specifications

|                 |   |
|-----------------|---|
| Input Voltage   | 120V / 60Hz, 277V 60Hz                                      |
| Lamp Type       | 0-10 V LED Lamps with or without Ballast, Forward Phase Cut |
| Wiring Type     | Terminals, Leads for Load                                   |
| Number of Poles | 3 Pole, 4 Wire  |
| Height          | 4.25 in.  |
| Depth           | 2.0 in.   |
| Width           | 2.5 in.   |
| Weight          | 0.20 lbs.   |

# BRYANT®