

Lighting Controls Residential Slide Dimmer Switch

200W LED/CFL, 600W Incandescent 1.5A

Single Pole, Three Way, 120 VAC

BRYANT®

Features

- Trim Adjustment for Fine Tuning
- Digital Circuit Controlled
- Decorator Slide Styling
- UL/cUL listed



Ordering Information

Description	Color	UPC	Catalog Number
Decorator Slide Dimmer 200W CFL/LED, 600W Incandescent	Ivory	783585565767	LCD150SI

Listings

UL/cUL listed

Online Resources

[eCatalog](#)

Specifications

Input Voltage	120V / 60Hz
Lamp Type	Dimmable, LED/CFL, Incandescent, Forward Phase Cut
Wiring Type	Terminals
Number of Poles	3 Pole, 4 Wire
Height	4.25 in.
Depth	2.0 in.
Width	2.5 in.
Weight	0.25 lbs.

BRYANT®