

Lighting Controls Residential Toggle Dimmer Switch

150W LED/CFL, 600W Incandescent 1.5A

Single Pole, Three Way, 120 VAC

BRYANT®

Features

- Trim Adjustment for Fine Tuning
- Digital Circuit Controlled
- Traditional Toggle Styling
- UL/cUL listed

Ordering Information

| Description | Color | UPC | Catalog Number |
|--|--------------|--------------|----------------|
| Toggle Dimmer 150W CFL/LED, 600W Incandescent | Light Almond | 783585565842 | LCD150TLA |



Online Resources

eCatalog

Listings

UL/cUL listed

Specifications

| | |
|-----------------|---|
| Input Voltage | 120V / 60Hz |
| Lamp Type | Dimmable, LED/CFL, Incandescent, Forward Phase Cut |
| Wiring Type | Terminals |
| Number of Poles | 3 Pole, 4 Wire |
| Height | 4.25 in. |
| Depth | 2.0 in. |
| Width | 2.0 in. |
| Weight | 0.20 lbs. |

BRYANT®