

## Lighting Controls Residential Rocker Dimmer Switch

300W LED/CFL, 600W Incandescent 1.5A

Single Pole, Three Way, 120 VAC

# BRYANT®

### Features

- Trim Adjustment for Fine Tuning
- In-use Indicator Light
- Digital Circuit Controlled
- Decorator Rocker Styling
- UL/cUL listed



### Ordering Information

Description	Color	UPC	Catalog Number
Decorator Rocker Dimmer 300W CFL/LED, 600W Incandescent, Indicator light	Light Almond	783585565873	LCD300DLA

### Online Resources

[eCatalog](#)

### Listings

UL/cUL listed

### Specifications

Input Voltage	120V / 60Hz
Lamp Type	Dimmable, LED/CFL, Incandescent, Forward Phase Cut
Wiring Type	Terminals
Number of Poles	3 Pole, 4 Wire
Height	4.25 in.
Depth	2.0 in.
Width	2.0 in.
Weight	0.25 lbs.

# BRYANT®