

TradeSelect  
Straight Blade Devices  
15A, 125V, 2 Pole, 3 Wire Grounding  
Tamper Resistant/ Weather-Resistant  
Decorator Duplex

# BRYANT

## Ordering Information

Device Color	UPC	Catalog Number
White	883778303128	RRD15SWWRTR

## Listings

NEMA WD1 and WD5, UL 498

## Specifications

Grade	Residential
Size	Standard Sized
Connection Type	Push and Side Wire
Mounting Type	Screw, Flush
Wattage	1,875 Watt
Wire Size	#14 AWG to #12 AWG
Material	Thermoplastic
NEMA Rating	5-15R

## Performance

### Electrical

Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

### Environmental

Flammability	UL 94 V-2
Operating Temperatures	Maximum continuous 75°C; minimum -40°C (w/o impact)



Dimensions in Inches (mm)

Bryant Electric • An affiliate of Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484  
Phone (800) 323-2792 • Specifications subject to change without notice